

https://www.phoenixcontact.com/us/products/0800300



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, yellow, unlabeled, can be labeled with: THERMOMARK E.SLEEVE, THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, unperforated, mounting type: slide-on, cable diameter range (automated processing): 0.8 ... 1.5 mm, cable diameter range: 0.8 ... 2.4 mm, Number of individual labels: 1, roll length: 30 m, text field height: 4 mm, text field width: 30000 mm

Product description

The continuous shrink sleeves in the WMS... product family, in size 2.4 ... 9.5, are suitable for automated processing with the THERMOMARK E. SLEEVE applicator. The continuous format of the material means that individual marker lengths can be realized. After the printing and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

Your advantages

- · Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- High flexibility, as individual marker lengths ranging from 3.45 mm ... 2000 mm (0.14" ... 78.7") can be realized in combination with the cutter and perforation cutter
- · As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 3:1
- · Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

Commercial data

Item number	0800300
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG14
Product key	BG2216
Catalog page	Page 227 (C-3-2019)
GTIN	4046356625975
Weight per piece (including packing)	203.5 g
Weight per piece (excluding packing)	195 g
Customs tariff number	39173200
Country of origin	CN



https://www.phoenixcontact.com/us/products/0800300



Technical data

Notes

Note on application	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
Material information	The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk. Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.

Product properties Product type

Туре	Shrink sleeve
Data management status	
Article revision	04
Marking	
Number of individual labels	1
Identification technology	Thermal transfer for rolls

Shrink sleeve

Dimensions

Width	4 mm
Text field width	30000.00 mm
Text field height	4.00 mm
Length of roll	30.00 m
External dimensions	
Outside diameter	0.8 mm 2.4 mm

Material specifications

Color	yellow (RAL 1018)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Components	halogen-free
Shrink temperature	> 85 °C

Cable/line

External cable diameter	0.8 mm 2.4 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish



https://www.phoenixcontact.com/us/products/0800300



Result	Test passed
result	1 oot passed
Scratch test for the determining scratch resistance	
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed
esafilm test	
Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed
JV resistance	
Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
emperature resistance	
Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed
/ipe resistance of inscriptions	
Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide



0800300

https://www.phoenixcontact.com/us/products/0800300

Mounting type

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2
Salt spray test	
Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h
Ambient temperature (operation) Recommended storage conditions	-55 °C 125 °C 23 °C/50 % relative humidity. Storage in a dry and dark place the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	5 years
andards and regulations	
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Wipe resistance	DIN EN 61010-

slide-on



0800300

https://www.phoenixcontact.com/us/products/0800300

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/0800300



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982_Vol2_Sec1



0800300

https://www.phoenixcontact.com/us/products/0800300

Classifications

UNSPSC 21.0

ECLASS

	ECLASS-11.0	27281102
	ECLASS-12.0	27281102
	ECLASS-13.0	27281102
ETIM		
	ETIM 9.0	EC001530
UN	SPSC	

39131500



https://www.phoenixcontact.com/us/products/0800300



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com