

https://www.phoenixcontact.com/us/products/0800377



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, perforated, mounting type: slide-on, cable diameter range: 3.2 ... 9.5 mm, lettering field size: 30 x 16 mm, Number of individual labels: 500

### Product description

Due to their ladder-style format, the preassembled shrink sleeves in the WMS... product family provide a good overview and facilitate quick use. After the printing and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

### Your advantages

- · Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- Ladder style design: For a good overview and to facilitate quick use, the sleeves are preassembled in cut lengths: 15 mm, 30 mm, or 60 mm
- · As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- · High diameter coverage with a shrink ratio of 3:1
- · Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

#### Commercial data

Item number	0800377
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG14
Product key	BG2216
Catalog page	Page 224 (C-3-2019)
GTIN	4046356626460
Weight per piece (including packing)	397 g
Weight per piece (excluding packing)	373.7 g
Customs tariff number	39173200
Country of origin	CN



https://www.phoenixcontact.com/us/products/0800377



### Technical data

#### Notes

Note on application	For the THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK ROLLMASTER 300/600, and THERMOMARK E.300 (D)/E.600 (D) roll printers, this material can only be processed outside of the printer using the integrated material dispenser pack.
Material information	The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk.
	Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.

# Product properties Product type

Туре	Shrink sleeve
Marking	
Number of individual labels	500
Number of individual labels per row	2
Identification technology	Thermal transfer for rolls

Shrink sleeve

### Dimensions

Width	16 mm
Length	30 mm
External dimensions	
Outside diameter	3.2 mm 0.5 mm

#### Material specifications

RoHS compliant	yes
Color	white
Material	Polyolefine
Base element material	polyolefine
Components	halogen-free

#### Cable/line

External cable diameter	3.2 mm 9.5 mm
-------------------------	---------------

### Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Scratch test for the determining scratch resistance	
Specification	DIN EN ISO 1518-1:2019-10 (following)



https://www.phoenixcontact.com/us/products/0800377



Requirements	≥ 5 N
Result	Test passed
Tesafilm test	
Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed
UV resistance	
Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Temperature resistance	
Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed
Wipe resistance of inscriptions	
Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
Testing in a condensation changing climate in the presence of	sulfur dioxide
Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S



https://www.phoenixcontact.com/us/products/0800377



Cycles	2
Salt spray test	
Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h
Ambient conditions	
Ambient temperature (operation)	-55 °C 125 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	5 years
tandards and regulations	
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
lounting	
Mounting type	slide-on



https://www.phoenixcontact.com/us/products/0800377



### **Approvals**

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/0800377



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982\_Vol2\_Sec1



https://www.phoenixcontact.com/us/products/0800377



### Classifications

UNSPSC 21.0

#### **ECLASS**

ECLASS-11.0	27281102	
ECLASS-12.0	27281102	
ECLASS-13.0	27281102	
ETIM		
ETIM 9.0	EC001530	
UNSPSC		

39131500



https://www.phoenixcontact.com/us/products/0800377



### Environmental product compliance

#### EU RoHS

20 1010	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU DE AGU GIALIG	
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com