

https://www.phoenixcontact.com/us/products/0800428



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, black, unlabeled, can be labeled with: THERMOMARK E.SLEEVE, THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLLMASTER 300/600, THERMOMARK ROLL X1, THERMOMARK ROLL, THERMOMARK ROLL 2.0, THERMOMARK W, THERMOMARK X1.2, unperforated, mounting type: slide-on, cable diameter range (automated processing): 1 ... 3 mm, cable diameter range: 1 ... 3.2 mm, Number of individual labels: 1, roll length: 120 m, text field height: 5 mm, text field width: 120000 mm

### Product description

The continuous shrink sleeves in the WMS... product family, in size 2.4 ... 9.5, are suitable for automated processing with the THERMOMARK E. SLEEVE applicator. The continuous format of the material means that individual marker lengths can be realized. After the printing and applying process, you have the option of shrinking the marked shrink sleeves by applying heat manually and thus fixing them on the cable/wire.

### Your advantages

- · Permanent and captive identification of single-core wires, wires, cables, pneumatic hoses, and other cylindrical objects
- High flexibility, as individual marker lengths ranging from 3.45 mm ... 2000 mm (0.14" ... 78.7") can be realized in combination with the cutter and perforation cutter
- · As an option, the sleeves can be shrunk by applying heat manually to fix the sleeve in position
- High diameter coverage with a shrink ratio of 3:1
- · Widely used and proven worldwide in control cabinet and machine building, the oil and gas industry, and the railway industry

### Commercial data

Item number	0800428
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG14
Product key	BG2216
Catalog page	Page 227 (C-3-2019)
GTIN	4046356626262
Weight per piece (including packing)	802 g
Weight per piece (excluding packing)	538 g
Customs tariff number	39173200
Country of origin	CN



https://www.phoenixcontact.com/us/products/0800428



### Technical data

#### Notes

Note on application	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
Material information	The specified minimum wire diameter of the shrink sleeve refers to its use as a marking material and does not guarantee any insulation characteristics once shrunk.  Depending on the processed material batch, as well as the storage and processing conditions, the maximum insertable wire diameter may be reduced.

# Product properties Product type

Туре	Shrink sleeve
Data management status	
Article revision	04
Marking	
Number of individual labels	1
Identification technology	Thermal transfer for rolls

Shrink sleeve

#### **Dimensions**

Width	5 mm
Text field width	120000.00 mm
Text field height	5.00 mm
Length of roll	120.00 m
External dimensions	
Outside diameter	1 mm 3.2 mm

### Material specifications

RoHS compliant	yes
Color	black (RAL 9005)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Components	halogen-free
Shrink temperature	> 85 °C

#### Cable/line

External cable diameter	1 mm 3.2 mm

### Environmental and real-life conditions



https://www.phoenixcontact.com/us/products/0800428



Result	Test passed
Scratch test for the determining scratch resistance	
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed
Fesafilm test	
Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed
JV resistance	
Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Comporaturo registance	
Femperature resistance Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed
Training 125 C (150 C)	Test passeu
Vipe resistance of inscriptions	
Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane	Test passed
[CAS No. 110-54-3]	
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l	Test passed
[CAS No. 1310-73-2]	
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed
Festing in a condensation changing climate in the presence of	f sulfur dioxide
Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S



0800428

https://www.phoenixcontact.com/us/products/0800428

Cycles	2
Salt spray test	
Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h
Ambient conditions	
Ambient temperature (operation)	-55 °C 125 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	5 years
andards and regulations	
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
ounting	
Mounting type	slide-on



0800428

https://www.phoenixcontact.com/us/products/0800428

### **Approvals**

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/0800428



CSA

Approval ID: 252259



cULus Recognized

Approval ID: E310982\_Vol2\_Sec1



0800428

https://www.phoenixcontact.com/us/products/0800428

### Classifications

UNSPSC 21.0

#### **ECLASS**

	ECLASS-11.0	27281102
	ECLASS-12.0	27281102
	ECLASS-13.0	27281102
ETII	М	
	ETIM 9.0	EC001530
UNS	SPSC	

39131500



0800428

https://www.phoenixcontact.com/us/products/0800428

### Environmental product compliance

#### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com