




Floor Mount System Floor Mount Column

| Appearance | Applicable light curtain | | Column height | Model |
|---|---------------------------------|---|---------------|------------|
| | F3SG-SR Safety Light Curtain | F3SG-PG Safety Multi-Light Beam | | |
|  | Protective height up to 0880 | F3SG-4PGA0670-2□ | 990 mm | F39-ST0990 |
| | Protective height up to 1280 | F3SG-4PGA0970-3A/3L F3SG-4PGA1070-4□ | 1,310 mm | F39-ST1310 |
| | Protective height up to 1520 | F3SG-4PGA1370-4□ | 1,630 mm | F39-ST1630 |
| | Protective height up to 1840 | --- | 1,950 mm | F39-ST1950 |
| | Protective height up to 2080 | --- | 2,270 mm | F39-ST2270 |

*1. Floor Mount Column, Mirror Column, Mount-Column Adjustable Base: Each model includes one product.
When using for both the emitter and receiver, order two sets.

*2. The mount-column adjustable base is sold separately.

Mirror Column


| Appearance | Applicable light curtain | | Column height | Model |
|--|---------------------------------|--|---------------|---------------|
| | F3SG-SR Safety Light Curtain | F3SG-PG Safety Multi-Light Beam | | |
|  (Operating range becomes 15% shorter than the rating) | Protective height up to 0880 | F3SG-4PGA0670-2A/2L | 990 mm | F39-SML0990 |
| | Protective height up to 1200 | F3SG-4PGA0970-3A/3L F3SG-4PGA1070-4A/4L | 1,310 mm | F39-SML1310 |
| | Protective height up to 1520 | F3SG-4PGA1370-4A/4L | 1,630 mm | F39-SML1630 |
| | Protective height up to 1840 | --- | 1,950 mm | F39-SML1950 |
|  (Operating range becomes 10% shorter than the rating) | --- | F3SG-4PGA0670-2A/2L | 990 mm | F39-PML0990-2 |
| | --- | F3SG-4PGA0970-3A/3L | 1,310 mm | F39-PML1310-3 |
| | --- | F3SG-4PGA1070-4A/4L | | F39-PML1310-4 |
| | --- | F3SG-4PGA1370-4A/4L | 1,630 mm | F39-PML1630-4 |

Note: The F3SG-SR Safety Light Curtain with the protective height of 1920 or more cannot be used.

*1. Floor Mount Column, Mirror Column, Mount-Column Adjustable Base: Each model includes one product.
When using for both the emitter and receiver, order two sets.

*2. The mount-column adjustable base is sold separately.

Mount-Column Adjustable Base

| Appearance | Application | Model |
|---|--|---------|
|  | Mounted to the floor mount column or mirror column. The angle and height of the column can be adjusted. | F39-STB |



*1. Floor Mount Column, Mirror Column, Mount-Column Adjustable Base: Each model includes one product.
When using for both the emitter and receiver, order two sets.

*2. The floor mount column and mirror column are sold separately.


Other Optional Accessories Common to F3SG-SR and F3SG-PG

Laser Alignment Pointer

- The laser alignment pointer is attached on the optical surface of the F3SG-SR/PG to help coarse adjustment of beams.

| Appearance | Specifications | Model |
|---|---|----------------|
|  | The laser alignment pointer can be attached to the front side of the F3SG-SR/PG. It can be used together with F39-ST. | F39-PTS |
|  | The laser alignment pointer can be attached to the F3SG-SR/PG with the spatter protection cover. | F39-PTG |

Lamp

| Appearance | Specifications | Model |
|---|--|-----------------|
|  | The lamp can be connected to emitter, receiver, or emitter/receiver and turned ON based on the operation of F3SG-SR/PG. The lamp can indicate red, orange, and green colors, to which three different states can be assigned. IP67 * rated when mated. | F39-SGLP |

* When the accessory is used, protect it from cutting oil.
Note: The Lamp does not support Bluetooth® communication.

F3SG-SR/PG

F3SG-SR-K

F3SG-SR and F3SG-PG
 Common to